



Polyamide/PEEK

Polyamide/PEEK

Polyamide/PEEK

PA
PEEK

Vorpolitur • pre-polishing • pré polissage



Glanzpolitur • shine polishing • poli brillant



Hochglanzpolitur • high shine polishing • lustrage



Info

4280 = Ø 80 mm = 1.400 rpm
 869 100/14 = Ø 100 mm = 1.400 rpm
 868 4'' x 50 H = Ø 100 mm = 1.400 rpm



ThermoPol Set

Inhalt/contents/ contenu
 1 x Polistar Lintygrau 90g
 2 x 4280
 1 x Polistar Creme 90g
 1 x 869 100/14
 1 x Polistar pro Rosa 150g
 1 x 868 4''x 50 H
 1 x PocketCard

Zirkoniumdioxid

Zirconium dioxide

Dioxyde de zirconium

ZrO₂

Feinstschleifen • Finest grinding • rectiflage fin



Hochglanzpolitur • high shine polishing • lustrage



Info

362 4 HP = Ø 4 mm = 10.000 rpm
 TORO 5 100 = Ø 17,5 mm = 10.000 rpm





PMMA/Komposite

PMMA/Composite


PMMA/Composite

PMMA
COMPOSITE


Vorpolitur • pre-polishing • pré polissage



Glanzpolitur • shine polishing • poli brillant



Hochglanzpolitur • high shine polishing • lustrage



Info

905.1 14 PP = Ø 14 mm = 5.000 rpm
 903.2 14 PP = Ø 14 mm = 5.000 rpm
 904.3 14 PP = Ø 14 mm = 5.000 rpm



HABRAS Disc Pro DCS Kit 14
 Inhalt/contents/contenu
 1 x 905.1 14 PP
 1 x 903.2 14 PP
 1 x 904.3 14 PP


Lithiumdisilikat

Lithium disilicate


Silicate de lithium

LiSi₂

Feinstschleifen • Finest grinding • rectifiage fin



Hochglanzpolitur • high shine polishing • lustrage



Polistar Pro Diamant



Info

367 4 HP = Ø 4 mm = 10.000 rpm
 TORO 5 102 = Ø 17,5 mm = 10.000 rpm